

Sumitomo Drive Technologies

»» Building Tomorrow Together

BRAND NEW Decentralized Drive Package DX-620



Our BRAND NEW Decentralized Drive Package will enhance operations by providing your conveyor systems with:

High Speed

Staff Efficiency


Flexibility

Energy Savings

BRAND NEW Decentralized Drive Package

VFD	Motors	Gearbox				
		Cyclo	Prest NEO	Hyponic	BBB	BBB-H
Motor Mount	IE3 Gearmotor	0	0	0	0	0
	IE5 Gearmotor	0	0	0	0	Upcoming
Wall Mount	IE3 & IE5 Gearmotor	0	0	0	0	0
	IE3 & IE5 Motor C-Face / NEMA Flange	0	0	0	0	0

Category	Item		Specification
VFD	Key features		DCC is designed to be easy to select, quick to install, simple to deploy, intuitive to commission and to protect the application it serves.
	Supply voltage		3phase AC380-480V, -15% ~ +10% 3phase AC200-240V, -15% ~ +10%
	Power range	Wall mount type	IE3 Induction motor: 0.5HP ~ 5HP IE5 Permanent magnet motor: 0.4HP ~ 5HP (Higher power coming soon)
		Motor mount type	IE3 Induction motor: 0.5HP ~ 4HP IE5 Permanent magnet motor: 0.4HP ~ 5HP
	Communication protocol		Ethernet/IP Profinet
	Interface		RS-485, USB-C, MR (Ethernet)
Applications			Belt conveyor, Chain conveyor, Screw conveyor, Baggage conveyor, Food processing



Contact us:
www.sumitomodrive.com

 **Inverter** Drives
 By Sumitomo Drive Technologies