


BEVEL BUDDYBOX®

H - SERIES



EXTREMELY EFFICIENT RIGHT-ANGLE SHAFT-MOUNTED REDUCERS AND GEARMOTORS.

FEATURES

- **Bevel Input + Helical Output = Extreme Efficiency**
Dependable hardened steel gearing
- **Lightweight, Compact Housing**
Easy installation with less load on the head shaft
Aluminum construction provides high thermal capacity
- **Maintenance Free and Lubed for Life**
Lowest total life cycle costs
- **Universal Mounting**
Install in any orientation without modification

TECHNICAL SPECS

- High speed / low reduction ratio 5:1 ~ 20:1
- Motor capacity: 3 ~ 15 HP
- Max input: 3600 motor RPM (120 Hz)
- C-face Quill or Coupled and Integral motor models available. Available hollow shafts include Easy Grip bushings, keyed hollow bores or shrink discs

INDUSTRY



FACTORY AUTOMATION



HIGH-SPEED UNIT HANDLING